

EA366FA-40～FB-400 研磨紙ロール

乾式向

乾・湿式向



EA366FA-40-400



EA366FB-120-400

好きなサイズにカットできるので経済的！

—— は廃番

品番	粒度	巻長	幅	品番	粒度	巻長	幅
EA366FA-40	#40	15M	75mm	EA366FB-120	#120	15M	75mm
EA366FA-60	#60			EA366FB-150	#150		
EA366FA-80	#80			EA366FB-180	#180		
EA366FA-100	#100			EA366FB-240	#240		
EA366FA-120	#120			EA366FB-320	#320		
EA366FA-150	#150			EA366FB-400	#400		
EA366FA-180	#180						
EA366FA-240	#240						
EA366FA-320	#320						
EA366FA-400	#400						

適合本体：研磨面幅75mm

EA162KK

