


# EA616GB-1~-12

(メガネレンチ)

○ クロム合金鋼

○ 12ポイント



	対辺	L	d1	d2	a1	a2	t	重量(g)
GB-1	1/4X5/16	180	11.8	13.1	7	7	20	61
GB-2	3/8X7/16	200	15.8	17.2	9	9	23	88
GB-3	1/2X9/16	220	20	21.3	9	10	25	131
GB-3A	9/16X5/8	245	21.3	25.3	10	12	27	168
GB-4	19/32X11/16	255	23.9	25.3	11	12	27	177
GB-4A	5/8X3/4	270	23.9	28	12	13	29	235
GB-5	11/16X13/16	300	25.3	30.7	12	13	31	280
GB-5B	3/4X7/8	300	28	32.1	13	14	31	299
GB-7	25/32X13/16	300	29.4	32.1	13	14	31	333
GB-8	7/8X15/16	330	32.1	34.7	14	14	34	363
GB-9	15/16X 1	330	34.7	37.3	14	15	34	419
GB-10	11/8X15/16	365	42.6	45.4	15	16	37	581
<del>GB-12</del>	<del>15/16X11/2</del>	<del>440</del>	<del>53</del>	<del>60</del>	<del>17</del>	<del>18</del>	<del>40</del>	<del>1076</del>

(単位mm)

廃番