

# Dリンク

D Link

材質：ステンレス SUS304

(mm)

品番	D	A	B	weight (g)	参考使用荷重		EA品番
					(kgf)	(kN)	
RD-3-15	3	15	12	3	20	0.20	EA638JD-1
RD-3-20	3	20	17	4	20	0.20	EA638JD-2
RD-4-25	4	25	22	9	40	0.39	EA638JD-5
RD-4-30	4	30	27	10	40	0.39	EA638JD-6
RD-4-35	4	35	32	12	40	0.39	EA638JD-7
RD-5-40	5	40	37	23	60	0.59	EA638JD-11
RD-6-50	6	50	47	43	80	0.78	EA638JD-15

