

EA725FA-69 端子&延長棒組合せチャート

測定範囲: 0-215mm

目盛: 0.01mm

ダイヤルインディケータ範囲: 5mm

ベース長さ: 100mm

① 8.9mm端子

② 13.9mm端子

③ 10mm延長棒

④ 20mm延長棒

⑤ 25mm延長棒

⑥ 50mm延長棒

⑦ 100mm延長棒

ダイヤルデプスゲージ(mm読取)のセットアップ範囲

No. 1 端子—0~5mm範囲

No. 2 端子—5~10mm範囲

例: 10~15mmの範囲(端子No.1+10mm延長棒)

範囲	端子		延長				
	No. 1	No. 2	10mm	20mm	25mm	50mm	100mm
0-5	○						
5-10		○					
10-15	○		○				
15-20		○	○				
20-25	○			○			
25-30	○				○		
30-35		○			○		
35-40	○		○		○		
40-45		○	○		○		
45-50	○			○	○		
50-55	○					○	
55-60		○				○	
60-65	○		○			○	
65-70		○	○			○	
70-75	○			○		○	
75-80	○				○	○	
80-85		○			○	○	
85-90	○		○		○	○	
90-95		○	○		○	○	
95-100	○			○	○	○	
100-105	○						○
105-110		○					○
110-115	○		○				○
115-120		○	○				○
120-125	○			○			○
125-130	○				○		○
130-135		○			○		○
135-140	○		○		○		○
140-145		○	○		○		○
145-150	○			○	○		○
150-155	○					○	○
155-160		○				○	○
160-165	○		○			○	○
165-170		○	○			○	○
170-175	○			○		○	○
175-180	○				○	○	○
180-185		○			○	○	○
185-190	○		○		○	○	○
190-195		○	○		○	○	○
195-200	○			○	○	○	○
200-205		○		○	○	○	○
205-210	○		○	○	○	○	○
210-215		○	○	○	○	○	○