



PROTAC HL[®] 5-X USB PROTAC HL[®] 5-X

MULTI-FUEL, HIGH LUMEN TACTICAL LIGHT

The 3,500 lumen ProTac HL 5-X is available two ways: The ProTac HL 5-X USB is a complete rechargeable system that includes two of our new 18650 USB batteries with an integrated USB charge port. The ProTac HL 5-X includes four CR123A lithium batteries.

Both feature MULTI-FUEL innovation that allows them to accept Streamlight's 18650 USB battery or CR123A lithium batteries, ensuring you'll always have a beam when you need it.



TEN-TAP [®] Programming: Choice of three operating modes: 1.) high/strobe/low; 2.) high only; 3.) low/medium/high
<ul style="list-style-type: none"> - High (18650 USB): 3,500 lumens; 51,000 candela; 452m beam; runs 1.25 hours - High (CR123A): 2,500 lumens; 37,000 candela; 385m beam; runs 1.5 hours - Medium: ,1,000 lumens; 14,100 candela; 237m beam; runs 2.5 hours (CR123A); runs 3 hours (18650 USB) - Low: 250 lumens; 3,620 candela; 120m beam; runs 10.5 hours (CR123A); runs 11.5 hours (18650 USB) - Strobe for signaling or disorienting: runs 1.5 hours (CR123A); runs 1.25 hours (18650 USB)
Optimized electronics provide thermal management and regulated intensity

Durable anodized machined aircraft aluminum construction IPX7; waterproof to 1m for 30 minutes; 1m impact resistance tested
9.53" (23.65 cm); 1 lb. 2.4 oz. (522g) with CR123A batteries; 1 lb. 3.4 oz. (550g) with Streamlight 18650 USB batteries
Limited Lifetime Warranty Visit www.streamlight.com for full warranty information
<ul style="list-style-type: none"> #88074 - ProTac HL 5-X w/ four CR123A lithium batteries and wrist lanyard - Clam #88075 - ProTac HL 5-X w/ four CR123A lithium batteries and wrist lanyard - Box #88080 - ProTac HL 5-X USB - two 18650 USB batteries, USB cord & wrist lanyard - Clam #88081 - ProTac HL 5-X USB - two 18650 USB batteries, USB cord & wrist lanyard - Box



PROTAC HL® 5-X USB | PROTAC HL® 5-X
MULTI-FUEL, HIGH LUMEN, PROFESSIONAL TACTICAL LIGHT



- Material/Lens** 6000 series machined aircraft aluminum with anodized finish
- Dims/Weight** Length: 9.53 in. (23.65 cm); Barrel Diameter: 1.24 in. (3.15 cm); Head Diameter: 2.35 in. (5.97 cm); Tri-Lobe Diameter: 2.29 in. (5.81 cm)
 Weight: ProTac HL 5-X USB: 1 lb 3.4 oz (550 grams) with two Streamlight rechargeable 18650 USB lithium ion batteries
 ProTac HL 5-X: 1 lb 2.4 oz (522 grams) with four CR123A lithium batteries
- Light Source** C4® LED technology for extreme brightness
- Output/ Runtime** Optimized electronics provides thermal management and regulated intensity.
 TEN-TAP® Programming: Choice of three operating modes:
 - High (18650 USB): 3,500 lumens; 51,000 candela; 452m beam; runs 1.25 hours
 - High (CR123A): 2,500 lumens; 37,000 candela; 385m beam; runs 1.5 hours
 - Medium: 1,000 lumens; 14,100 candela; 237m beam; runs 2.5 hours (CR123A); runs 3 hours (18650 USB)
 - Low: 250 lumens; 3,620 candela; 120m beam; runs 10.5 hours (CR123A); runs 11.5 hours (18650 USB)
 - Strobe for signaling or disorienting: runs 1.5 hours (CR123A); runs 1.25 hours (18650 USB)
- Switch** Multi-function, easy access head mounted push-button switch. One handed operation of momentary, variable intensity or strobe mode. TEN-TAP® Programmable switch allows user selection of one of three different programs: high/strobe/low (factory default), high only, or low/med/high
- Battery** Multi-fuel – uses two Streamlight rechargeable 18650 USB lithium ion batteries; also accepts four CR123A lithium batteries
- Features**
 - IPX7; waterproof to 1m for 30 minutes; 1m impact resistance tested
 - LED Solid State Power Regulation provides maximum light output throughout battery life
 - Anti-roll face cap
 - Sure grip rubber sleeve
 - Serialized for positive identification.
- Approvals** Meets applicable European Community directives. CEC Compliant (ProTac HL® 5-X USB only)
- Warranty** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
ProTac HL 5-X with four CR123A lithium batteries and wrist lanyard - Clam	080926-88074-0	88074
ProTac HL 5-X with four CR123A lithium batteries and wrist lanyard - Box - Black	080926-88075-7	88075
ProTac HL 5-X USB, includes two 18650 USB battery, dual USB cord and wrist lanyard - Clam	080926-88080-1	88080
ProTac HL 5-X USB, includes two 18650 USB battery, dual USB cord and wrist lanyard - Box	080926-88081-8	88081