

## **STYLUS PRO® USB - OPERATING INSTRUCTIONS**

### **Operation**

Push-button tail switch – momentary or constant on operation.

O-ring sealed, sliding cover protects the light's USB charging port from debris and water infiltration.

### **Battery**

Uses Streamlight's Lithium Ion cell pack with on-board safety circuit. It is rechargeable up to 300 times.

**NOTE:** When you get to 300 charges, the battery will take approximately 70% of the original charge value.

### **Charging**

Slide the head cover back on the light until it stops to expose the USB connector and charge indicator LED. Using the supplied cord, plug the USB connector into the mating socket on the light. Plug the standard USB connector into a USB port on your computer or other USB-accessible port.

If you have Streamlight's USB/AC wall plug adaptor, you can plug the USB connector into the adapter and charge the light using AC power.

**NOTE:** The light does not need to be in the off position to charge the light; however, if the light is on (lit) when the USB cord is plugged into the USB power source, the light will extinguish. When the light is unplugged from the USB power source, the light will come back on.

### **Charge Time**

The light has a digital control circuit that prevents overcharge. The battery fully recharges in 2.5 hours and charges the battery in the light.

**NOTE:** The 2.5 hour charge time assumes 500mA output USB connection. (USB power ports can range from 100 to 500 mA.)

### **Charge Indication LED**

Light features a charge indicator LED:

- LED Red: Charging
- LED Green: Charged

**NOTE -** If there is no battery in the light, the indicator LED will light up Orange.

### **Run Time Note**

The light drops off dramatically in the last 30 minutes. There is "no end of run time notification;" the light simply turns off.