

EA949DB-6 ~ 35 穴用スナップリングセット

材 質 : バネ鋼(S65C 硬度HRc 44 - 52)

サイズ

	適合穴径	止め輪					適用する穴		
		d 3	t	b	a	d 0	d 2	m	n
EA949DB-6	6	6.7	0.4	0.7	1.6	0.8	6.25	0.5	0.5
EA949DB-7	7	7.7	0.4	0.8	1.7	0.8	7.3	0.5	0.5
EA949DB-8	8	8.8	0.4	0.9	1.7	0.8	8.4	0.5	0.6
EA949DB-9	9	9.8	0.6	1.1	2.2	0.8	9.4	0.7	0.6
EA949DB-10	10	10.7	1.0	1.5	2.8	1.2	10.4	1.15	1.5
EA949DB-11	11	11.8	1.0	1.5	3.0	1.2	11.4	1.15	1.5
EA949DB-12	12	13.0	1.0	1.7	3.1	1.5	12.5	1.15	1.5
EA949DB-13	13	14.1	1.0	1.7	3.1	1.5	13.6	1.15	1.5
EA949DB-14	14	15.1	1.0	1.9	3.6	1.7	14.6	1.15	1.5
EA949DB-15	15	16.2	1.0	1.9	3.6	1.7	15.7	1.15	1.5
EA949DB-16	16	17.3	1.0	1.9	3.7	1.7	16.8	1.15	1.5
EA949DB-18	18	19.5	1.0	2.4	4.0	1.7	19.0	1.15	1.5
EA949DB-19	19	20.5	1.0	2.5	4.0	2.0	20.0	1.15	1.5
EA949DB-20	20	21.5	1.0	2.5	4.0	2.0	21.0	1.15	1.5
EA949DB-21	21	22.5	1.0	2.5	4.1	2.0	22.0	1.15	1.5
EA949DB-22	22	23.5	1.0	2.5	4.1	2.0	23.0	1.15	1.5
EA949DB-24	24	25.9	1.2	2.5	4.3	2.0	25.2	1.35	1.5
EA949DB-25	25	26.9	1.2	3.0	4.4	2.0	26.2	1.35	1.5
EA949DB-26	26	27.9	1.2	3.0	4.6	2.0	27.2	1.35	1.5
EA949DB-27	27	29.1	1.2	3.0	4.6	2.0	28.4	1.35	1.5
EA949DB-28	28	30.1	1.2	3.0	4.6	2.0	29.4	1.35	1.5
EA949DB-30	30	32.1	1.2	3.0	4.7	2.0	31.4	1.35	1.5
EA949DB-32	32	34.4	1.2	3.5	5.2	2.5	33.7	1.35	1.5
EA949DB-34	34	36.5	1.5	3.5	5.2	2.5	35.7	1.65	2.0
EA949DB-35	35	37.8	1.5	3.5	5.2	2.5	37.0	1.65	2.0

