

## ワッシャーサイズ表

呼び	ISO (0000)	ISO小形 (0001)	JIS (0010)	JIS小形 (0011)
1		1×2.5×0.3		
1.2		1.2×2.8×0.3		
1.4		1.4×3×0.3		
1.6		1.6×3.8×0.3		
2	2×5×0.3	2×4.3×0.3	2×6×0.4	2×4.3×0.4
2.3	2.3×6.5×0.5	2.3×4.6×0.5	2.3×7×0.5	2.3×4.6×0.4
2.5	2.5×6.5×0.5	2.5×5×0.5		
2.6	2.6×6.5×0.5	2.6×5×0.5	2.6×7.5×0.5	(2.6×5×0.5)
3	3×7×0.5	(3×6×0.5)	3×8×0.5	3×6×0.5
3.5	(3.5×9×0.5)	(3.5×7×0.5)	3.5×9×0.5	3.5×7×0.5
4	4×9×0.8	4×8×0.8	4×10×0.8	4×8×0.5
5	5×10×1.0	(5×10×1.0)	5×12×0.8	5×10×0.8
6	6×12.5×1.6	6×11.5×1.6	6×13×1.0	6×11.5×0.8
8	8×17×1.6	8×15.5×1.6	8×18×1.6	8×16×1.2
10	10×21×2.0	10×18×2.0	10×22×1.6	10×18×1.6
12	12×24×2.5	12×21×2.5	12×26×2.3	12×22×2.3
W <sup>1</sup> / <sub>2</sub>			13.5×26×2.3	
14	15×28×2.5	15×24×2.5	15×30×2.6	15×26×2.3
16	17×30×3.0	17×28×3.0	17×32×2.6	17×30×2.6
18	19×34×3.0	19×30×3.0	19×36×2.6	19×32×2.6
20	21×37×3.0	21×34×3.0	21×40×3.2	21×36×2.6
22	23×39×3.0	23×37×3.0	23.5×44×3.2	23.5×40×3.2
24	25×44×4.0	25×39×4.0	25.5×48×4.0	25.5×44×3.2
27	28×50×4.0	28×44×4.0	28.5×52×4.0	
30	31×56×4.0	31×50×4.0	31.5×58×4.5	
33	34×60×5.0	34×56×5.0	34.5×62×4.5	
36	37×66×5.0	37×60×5.0	38×68×5.0	
39	40×72×6.0	40×66×6.0	41×72×5.0	
42	43×78×7.0		44×78×6.0	
45	46×85×7.0		47×82×6.0	
48	50×92×8.0		50×88×6.0	
52	54×98×8.0		54×95×6.0	
56	58×105×9.0			
W2 <sup>1</sup> / <sub>4</sub>			60×103×8.0	
60	62×110×9.0			
W2 <sup>1</sup> / <sub>2</sub>			67×115×8.0	
64	66×115×9.0			
68	70×120×10.0			
W2 <sup>3</sup> / <sub>4</sub>			73×125×8.0	
72	74×125×10.0			
76	78×135×10.0			
W3 <sup>*</sup>			80×132×8.0	
80	82×140×12.0			

### 角ワッシャー

呼び	大形 (W0-0500)	小形 (W0-0501)
M6、 <sup>1</sup> / <sub>4</sub>	6.6×20×2.3	6.6×17×1.2
M8、 <sup>5</sup> / <sub>16</sub>	9×26×2.3	8.5×23×1.6
M10、 <sup>3</sup> / <sub>8</sub>	11×32×2.3	11×28×1.6
M12、 <sup>1</sup> / <sub>2</sub>	13.5×40×3.2	14.5×35×2.3
M14	16×44×3.2	16×40×3.2
M16、 <sup>5</sup> / <sub>8</sub>	18×52×4.5	18×45×3.2
M20、 <sup>3</sup> / <sub>4</sub>	22×62×6.0	22×56×4.5
M22、 <sup>7</sup> / <sub>8</sub>	24×68×6.0	22×64×4.5
M24	26×72×6.0	26×68×6.0
M27	30×80×6.0	
M30	33×90×6.0	
M36	39×110×8.0	

ステンW(JIS薄口) W0-02-0015
8×18×1.2
12×26×2.0
16×32×2.0

記号変更		
種類	旧記号	新記号
耐密用テーパめねじ	PT	Rc
耐密用平行めねじ	PS	Rp
機械的結合用平行めねじ	PF	G