



# EA164FB-30~-90 (1")インパクトソケット

- 6ポイント
- 差边角 1"



	サイズ(mm)	D1(mm)	D2(mm)	l(mm)	L(mm)	適用ピン	適用Oリング	重量(g)
EA164FB-30	30	49	54	21	62	EA164AA-6A	EA164A-45B	657
EA164FB-31	31	50.3	54	21	62			687
EA164FB-32	32	51.5	54	21	62			685
EA164FB-33	33	52.8	54	21	62			685
EA164FB-34	34	54	54	21	62			690
EA164FB-35	35	55.3	54	21	62			710
EA164FB-36	36	56.5	54	21	62			712
EA164FB-37	37	57.8	54	21	62			735
EA164FB-38	38	59	54	25	66			720
EA164FB-40	40	61.5	54	25	66			850
EA164FB-41	41	62.8	54	25	66			850
EA164FB-42	42	64	54	25	66			905
<del>EA164FB-43</del>	<del>43</del>	<del>65.3</del>	<del>54</del>	<del>27</del>	<del>68</del>			<del>977</del>
EA164FB-45	45	67.8	54	27	68			963
EA164FB-46	46	69	54	29	70			1010
EA164FB-47	47	70.3	54	36	70			997
EA164FB-48	48	71.5	54	35	70			990
<del>EA164FB-50</del>	<del>50</del>	<del>74</del>	<del>54</del>	<del>35</del>	<del>70</del>			<del>1065</del>
<del>EA164FB-52</del>	<del>52</del>	<del>76.5</del>	<del>54</del>	<del>40</del>	<del>75</del>			<del>1185</del>
<del>EA164FB-54</del>	<del>54</del>	<del>79</del>	<del>54</del>	<del>40</del>	<del>75</del>			<del>1252</del>
<del>EA164FB-55</del>	<del>55</del>	<del>80.3</del>	<del>54</del>	<del>39</del>	<del>75</del>			<del>1260</del>
<del>EA164FB-56</del>	<del>56</del>	<del>81.5</del>	<del>54</del>	<del>39</del>	<del>75</del>			<del>1277</del>
EA164FB-58	58	84	54	39	75			1340
EA164FB-60	60	86.5	54	39	75			1400
EA164FB-62	62	89	54	38	75			1410
EA164FB-63	63	90.3	54	38	75			1383
EA164FB-65	65	92.8	54	38	75			1630
<del>EA164FB-68</del>	<del>68</del>	<del>96.5</del>	<del>54</del>	<del>37</del>	<del>75</del>			<del>1583</del>
<del>EA164FB-70</del>	<del>70</del>	<del>99</del>	<del>54</del>	<del>37</del>	<del>75</del>	<del>1625</del>		
EA164FB-75	75	105.3	86	39	80	EA164AA-6B	EA164A-75	2675
EA164FB-80	80	111.5	86	44	85			2996
EA164FB-85	85	117.8	86	46	90			3378
<del>EA164FB-90</del>	<del>90</del>	<del>124</del>	<del>86</del>	<del>51</del>	<del>95</del>			<del>3871</del>


(例)



インパクトソケット用Oリング(別売)



インパクトソケット用ピン(別売)



インパクトソケット(別売)

必ずインパクトソケット用ピン、Oリングを併用してください。

— :取扱中止商品