


# 割ピン (EA949WP-161 ~ 550)



寸法単位(mm)

品番	入数	穴径	全長		d		D		a	H	
			基準寸法	許容差	基準寸法	許容差	基準寸法	許容差		約	最大
EA949WP-161	400	1.6	15	±0.8	1.4	0 / -0.1	2.8	0 / -0.4	3.2	2.5	1.2
EA949WP-220	330	2.0	20	±0.8	1.8	0 / -0.1	3.6	0 / -0.4	4.0	2.5	1.2
EA949WP-320	120	3.0	20	±0.8	2.8	0 / -0.2	5.6	0 / -0.6	6.0	3.2	1.6
EA949WP-325	180	3.0	25	±0.8	2.8	0 / -0.2	5.6	0 / -0.6	6.0	3.2	1.6
EA949WP-330	100	3.0	30	±0.8	2.8	0 / -0.2	5.6	0 / -0.6	6.0	3.2	1.6
EA949WP-350	100	3.0	50	±0.8	2.8	0 / -0.2	5.6	0 / -0.6	6.0	3.2	1.6
EA949WP-353	90	3.5	30	±0.8	3.3	0 / -0.2	6.6	0 / -0.7	7.0	3.2	1.6
EA949WP-435	90	4.0	35	±1.2	3.7	0 / -0.2	7.4	0 / -0.9	8.0	4.0	2.0
EA949WP-440	80	4.0	40	±1.2	3.7	0 / -0.2	7.4	0 / -0.9	8.0	4.0	2.0
EA949WP-454	55	4.5	45	±1.2	4.1	0 / -0.2	8.2	0 / -0.9	9.0	4.0	2.0
EA949WP-530	35	5.0	30	±1.2	4.6	0 / -0.2	9.2	0 / -1.2	10.0	4.0	2.0
EA949WP-550	25	5.0	50	±1.2	4.6	0 / -0.2	9.2	0 / -1.2	10.0	4.0	2.0

材質・・・鉄 (六価クロメートメッキ)

規格・・・JIS B 1351