

Kenko

galleryeye

取扱説明書

このたびは、遠近両用単眼鏡「ギャラリーアイ」をお買い上げいただきありがとうございます。この単眼鏡を末永くご愛用いただければ幸いです。ご使用の際は、この取扱説明書をよくお読みの上、正しくお使いください。

安全上のご注意 ー必ずお読みくださいー

本製品を安全にご使用いただくために、下記の項目をご使用前に必ずお読みになり、正しくお使いください。本製品を正しくお使いいただき、お使いになる人や他の人々への危害と財産への損害を未然に防止するために、次に説明しています。

警告 この指示にしたがわないで誤った取扱いをすると、人が死亡または重傷を負う可能性があります。



●本製品で太陽を絶対に見ないでください。失明や永久視力障害の原因となります。

注意 この指示にしたがわないで誤った取扱いをすると、人が障害を負う可能性があります。また、物的損害が発生する可能性があります。

- 取扱説明書を必ずお読みください。
- 本製品を落としたりぶつけたりして強い振動や衝撃を与えないでください。
- 本製品を不安定な位置に置かないでください。倒れたり落ちたりして、けがの原因になることがあります。
- 本製品を直射日光のあたるところに置かないでください。火災の原因になることがあります。
- 運転中または歩行中に本製品を使用しないでください。衝突、転倒し、けがの原因となる場合があります。
- ゴム見口の場合、長時間使用を繰り返しますと、皮膚に炎症を起こすことがあります。もし疑わしい状態があらわされましたら、ただちに医師にご相談ください。
- 部品など小さなお子様があやまって飲むことがないようにしてください。万一お子様が飲み込んだ場合、ただちに医師に相談してください。
- ポリ袋（包装用）などを小さなお子様の手の届くところに置かないでください。口にあてて窒息の原因になることがあります。
- ストラップを持って振り回さないでください。他人に当たり怪我の原因となる場合があります。

- ・本書はギャラリーアイ「4x12」「6x16」の共通取扱説明書です。一部、色や形状などが異なる場合もありますが、使用方法は同じです。
- ・本書に記載された商品の仕様、デザイン、その他の内容については予告なく変更されることがあります。
- ・本製品の使用に際しては、本書に記載した使用方法にしたがってご使用願います。特に「安全上のご注意」に記載された内容につきましては厳守してください。
- ・本書の内容につきましては万全を期して作成しておりますが、万一ご不審な点や誤り、記載漏れなどお気づきの点がございましたらご連絡ください。
- ・本製品の不適切な使用により、万一損害が生じたり、逸失利益、または第三者のいかなる請求に関し、当社では一切その責任を負いかねますのでご了承ください。


【仕様と性能】

仕様	型名	4x12	6x16
倍率		4倍	6倍
対物レンズ有効径		12mm	16mm
実視界		12°	9.3°
1000m先の見える範囲		210.2m	162.7m
最短焦点距離		19cm	25cm
サイズ（ストラップ取付け部除く）		φ3.1 x 6.3cm	φ3.1 x 7.5cm
重量		53g	61g

※製品の仕様及び外観は改良のため予告なく変更することがあります。

【各部名称】

- ①対物レンズ
- ②握りグリップ
- ③ゴム見口（焦点調整リング）
- ④接眼レンズ
- ⑤ストラップ取付け部




【使い方】


1. 握りグリップを指で押さえて固定し、ゴム見口部を軽く目に当てます。
2. ゴム見口（焦点調整リング）を回し、目標にピントを合わせます。
3. ゴム見口（焦点調整リング）を繰り出すと近距離、縮めれば遠距離にピントが合います。
※焦点調整リングを全部繰り出したところで至近距離約19cm(4x12)、約25cm(6x16)からピントが合います。
4. メガネをかけた人は、ゴム見口を折り曲げて使用すると全視野がけられなくて見ることができます。

3. この間の繰り出し量で、遠くから近くまで距離変化にも対応してピントが合う設計です。（全機種共通）


●遠距離の場合




●近距離の場合



4. 通常の状態




折り込んだ状態



【ストラップの取付け方】

1. 右の図のように、ストラップ取付け部にストラップの紐部分を通します。
2. 通した紐部分に、ストラップを通します。



【手入れと保存】

◆レンズの汚れ

レンズについたホコリや汚れなどは、プロアーや筆先で払い、柔らかい布で拭いてください。また、指紋や油などがついたときは少量のアルコール液を布にひたして拭き取ってください。

◆ケースの格納

繰り出した鏡筒をもとの位置まで戻してください。無理に納めると破損や故障の原因になります。

◆湿気に対する注意

レンズやプリズムの大敵は湿気です。カビなどが生じることがあります。風通しの良いところへ保管してください。



Kenko Tokina Co., Ltd.

株式会社 ケンコー・トキナー TOKYO/JAPAN
〒164-8616 東京都中野区中野 5-68-10 KT 中野ビル

ケンコー・トキナー ホームページ
<http://www.kenko-tokina.co.jp/>

フリーダイヤル（無料）※海外からおよびIP電話では接続できません

0120-775-818

携帯電話・PHS・IP電話をご利用の場合

03-6840-3389（通話料がかかります）

●受付時間 9:15 ~ 17:30（土曜日・日曜日・祝日・年末年始・夏期休業等を除く）

Kenko


galleryeye

Instruction manual

Thank you for purchasing Kenko galleryeye monocular for both short and long range observations. For a correct and safe use of Kenko galleryeye monocular, please read carefully this instruction manual beforehand.

Safety precautions -Be sure to read-

Be sure to read the following precautions in advance for proper and safe use. The following explains how to safely use this product and prevent harm to users and third parties, as well as damage to property.

Warning Not adhering to these instructions and handling the product wrongly may lead to death or serious injury. 

• **Never look at the sun or an intense light source with this product. It may lead to vision loss or permanent visual impairment.**

Cautions Not adhering to these instructions and handling the product wrongly may lead to bodily injury. Property damage may also occur.

- Be sure to read this instruction manual.
- Do not subject this product to any strong vibrations or shocks by dropping it or knocking it against anything.
- Do not place this product in an unstable position. It may fall over or drop, leading to injury.
- Do not place this product in direct sunlight. It may lead to a fire.
- Do not use this product while driving or walking. It may lead to injury, due to a sudden collision or fall.
- Repeatedly using the rubber eyecups for extended periods of time may cause inflammation of the skin. If in doubt, immediately contact a doctor.
- Take care that small children do not mistakenly ingest any small parts. If a child happens to ingest it, immediately contact a doctor.
- Do not place the wrapping plastic bags in reach of small children. They may place it over their mouth, leading to suffocation.
- Do not swing it around by the strap. It may strike a third person, leading to injury.

- This instruction manual applies for both 4x12 and 6x16 models. Though there may be differences in color and shape, the content is the same.
- The product specifications, design, and other content included in this document may change without notice for modification.
- When using this product, please follow the instructions listed in this document. Comply strictly to the content listed in "Safety Precautions" in particular.
- Please notify us in the event you notice something suspicious, a mistake, or any missing information.
- Please be advised that we are not liable for any damage, lost profits, or requests from a third party incurred from improper use of this product.


[Specifications]

Model	4 x 12	6 x 16
Magnification	4 x	6 x
Objective lens diameter	12mm	16mm
Field of view	12°	9.3°
FOV at 1000m	210.2m	162.7m
Closest focusing distance	19 c m	25 c m
Size(excluding strap attachment)	φ 3.1 x 6.3 c m	φ 3.1 x 7.5 c m
Weight	53 g	61 g

※Product specifications and exterior design may change without prior notice due to modifications.

[Parts]

- ① Objective lens
- ② Handgrip
- ③ Rubber eye-cup (focus adjusting ring)
- ④ Eyepiece
- ⑤ Strap attachment section




[How to use]


1. Hold the handgrip tight and carefully bring the monocular up to your eyes.
2. Adjust the focus by rotating the rubber eye-cup (focus adjusting ring).
3. You can focus close and far by rotating the eye-cup (focus adjusting ring).
Note: when the eye-cup (focusing adjusting ring) is completely extended, you can focus from a close range of approx. 19 cm (for 4x12 model) and 25cm (for 6x16 model).

3. The optics is designed to have both far and close objects in focus within the extending range of the eye-cup.


● Far focusing



● Close focusing





4. The rubber of the eye-cup can be folded. This is particularly convenient when wearing glasses, as it allows observation without vignetting on the field of view.



[How to attach the strap]

1. Pass the strap string through the strap attachment section, as shown in the picture on the right.
2. Pass the opposite end of the strap through the strap string and pull to tighten the knot.



[Product care and storage]

◆ Lens cleaning

Remove dirt and dust from the lens with a blowing device or brush, and wipe gently with a soft cloth. To remove fingerprints or smudges, wipe the lens gently with a soft cloth dipped in a small amount of alcohol.

◆ Storage conditions

-When storing the monocular in its case, make sure to shorten the eye-cup. If forced, it may cause damage or malfunctioning.

-Humidity is the worst enemy for lenses and prisms, as it may generate mold. To avoid this, please make sure to store this product in a well-ventilated place.

 Kenko Tokina Co., Ltd.

KT Nakano Building, 5-6B-10, Nakano, Nakano-ku, Tokyo, 164-8616, JAPAN

Kenko Global Website
www.kenkoglobal.com